PREFABRICATED FARADAY CAGES

Our prefabricated self-standing modular Faraday cages offer superior screening of RF/LF/HF signals, e.g. for R&D, TEMPEST and Testing purposes





A freestanding (independent of the host building) prefabricated modular Faraday cage provides a superior screening of RF-signals and is applicable in a wide range of situations for a wide range of purposes.

The modular Faraday cage is designed to meet or even exceed the vast majority of shielding requirements requested in todays society.

APPLICATIONS

- LF/RF/HF tests
- EMC test labs
- Wireless product testing
- EMI/RFI shielded server rooms
- Protection of sensitive information (NATO TEMPEST standards)
- HEMP & EMP protection
- Neuroscience laboratories
- Cellular communication devices
- Immunity & emission test chambers
- Anechoic chambers
- MRI rooms
- Neurology labs

ADVANTAGES

- Freestanding construction
- High shielding performance without deterioration
- Easy to modify, enlarge or reinstall with conventional hand power tools
- Optionally supplied as a kit for assembly by the user
- Easy to mount by skilled local workers
- Many sizes directly available from stock, custom designs available within a few weeks
- Standard 10 years warranty, moving parts and electronics excluded

OPTIONS

Examples of several options are listed below:

- (Customized) shielded honeycomb ventilation panels
- Shielded doors
 - Automatic sliding doors
 - Double leaf door
 - Double door as in sluice-gate construction
- Bolts on the in-or outside for construction convenience
- Shielded piping for water or gas flow
- Acoustic panels on the inside
- Lightweight version
- Entry panel fitted with:
 - Power filters, single- or three phase +N (specify amperage, voltage and frequency)
 - Feed through signal filters
 - Wave guides for passage of fiber-optic cables
 - Feed through penetration
 - (e.g. SMA- or BNC connector)
 - Grounding bolt

STANDARD CAGE DIMENSIONS

Our prefabricated Faraday cages can be made in almost any size. By default, the following prefabricated Faraday cage panels are in stock and can be delivered quickly. A Faraday cage can also be produced according to the customers specifications. Any time you can enlarge it, make it smaller and create different shapes.


Length (mm)	Width (mm)	Height (mm)
1090	1170	2315 / 2840 / 3405
1090	2260	2315 / 2840 / 3405
2180	2260	2315 / 2840 / 3405
3270	2260	2315 / 2840 / 3405
3270	3350	2315 / 2840 / 3405
4360	2260	2315 / 2840 / 3405
4360	4440	2315 / 2840 / 3405
5450	5530	2315 / 2840 / 3405

» PREFABRICATED FARADAY CAGES


SHIELDING PERFORMANCE*

Shielding performance graph of a standard prefabricated cage vs a high performance Faraday cage.

Prefabricated Faraday cage [Magnetic]







ADDITIONAL PRODUCT INFORMATION AND MATERIAL USE

The prefabricated Faraday cage consists of galvanized (2 mm thick) Mu-Ferro steel shielding panels. The galvanization ensures excellent resistance to corrosion.

Gaskets are applied between all panels of the Faraday cage to ensure a good electrical conductivity and a good seal between the panels. The gaskets are produced in our gasket production facility.

To ensure a high shielding performance over time, the bare modular prefabricated Faraday cage construction does not contain any wooden parts that could be affected by variations in temperature or moisture.

In short, the corrosion resistant panels guarantee excellent electrical conductivity and provide a high shielding effectiveness.

IN HOUSE PRODUCTION FACILITY

We produce Faraday cages daily and are therefore able to quickly deliver standard sizes from our large stock. The panels we keep in stock can also be adjusted quickly according to your needs, for example for the input of power line filters, waveguides, honeycomb ventilation panels, etc. These custom sizes can be produced in several weeks from order date. When desired, the Faraday cage can also be adjusted on location.

We can deliver a cage in any requested size with any requested attenuation. If a straightforward cage with low attenuation requirements is desired, we can deliver the cage standard from stock for an attractive price.

The modular panels can be shipped and assembled by the customer or under supervision of our engineers, anywhere in the world.



FULLY FINISHED INTERIOR

We can also provide a fully finished interior. The walls and ceiling of the cage are then completely decorated with wood, and the floor with carpeting so that the shielding panels of the cage are no longer visible.

Below is an example of a prefabricated Faraday cage before and after its interior finish.

Air conditioning, lighting, wall outlets cable ducts, work tables and many more features can be taken into account in this complete interior finish.

HOW TO ORDER

For a quotation of a prefabricated Faraday cage please send an email with drawings of the room that requires shielding.

In case no drawings of the room are available, we must know the amount of square meters that require shielding. Also indicate the application of the shielded room. This enables us to think about the right solution from scratch.



2

Ph: +31(0)78 - 204 90 00 **Fax:** +31(0)78 - 204 90 08